

RBRvirtuoso3

# SINGLE CHANNEL LOGGER



The RBR*virtuoso*<sup>3</sup> single channel loggers offer flexible measurement schedules, standard sampling up to 2Hz, optionally up to 32Hz, large memory, extra power for extended deployments, twist activation, and USB-C download for large data files.

## **FEATURES**













## The RBRvirtuoso<sup>3</sup> is available in the following configurations:

- Temperature
- Depth
- Conductivity
- Tides
- Waves
- Dissolved O<sub>2</sub>
- Turbidity
- Fluorescence
- ► T-string

- ▶ pH
- ► ORP (RedOx)
- PAR

The RBRvirtuoso<sup>3</sup> makes it easy to configure the optimum sampling regime for your measurements. The large data storage capacity and fast download ability facilitate long deployments with higher sampling rates.

Almost every sensor from RBR can be interfaced to the RBR*virtuoso*<sup>3</sup>. Dataset export to Matlab, Excel, OceanDataView<sup>®</sup>, or text files makes post processing with your own algorithms effortless.





## SINGLE CHANNEL LOGGER

## MEASURE MORE, DEPLOY LONGER, DOWNLOAD FASTER

## **Specifications**

#### Physical

Power: 8 AA cells
Storage: 240M readings
Communication: USB-C or RS-232/485
Clock drift: ±60 seconds/year

Depth rating: 750m (plastic) or 10,000m (Ti)
Housing: Plastic or titanium
~340mm x Ø63.3mm /
~ Ø60.3mm (Ti)

### **Example Sensors**

#### Pressure

Range: 20 / 50 / 100 / 200 / 500 / 750

1000 / 2000 / 4000 / 6000 /

10,000m (dbar)

Initial accuracy: ±0.05% FS (full scale)

Resolution: <0.001% FS
Typical stability: 0.05% FS
Time constant: <0.01s

#### Temperature

Range:  $-5^{\circ}$ C to  $35^{\circ}$ C Initial accuracy:  $\pm 0.002^{\circ}$  Resolution:  $0.00005^{\circ}$ C

Time constant: ~1s (standard) or ~0.1s (option)

Typical stability: 0.002°C per year

#### Dissolved Oxygen (OxyGuard®)

Range: 0 to 600%

Accuracy: ±2% O<sub>2</sub> saturation (5°C to

25°C)

Resolution: 1% of saturation

Response time: ~10s, 90% step change @

20°C

#### Turbidity (Seapoint Sensors)

Light source: 880nm Time constant: 0.1s

Linearity: <2% deviation 0-1250 FTU

#### Fluorescence (Seapoint Sensors)

Excitation: Various wavelengths

Time constant: 0.1s

Range: 0.02μg/l to 150μg/l

#### Contact RBR for other sensor options.

## **Options**

- Wi-Fi communication
- ▶ |fast8, |fast16 or |fast32Hz sampling for profiling
- External data and power connector with USB, RS-232, or RS-485



### RBR Ltd

95 Hines Road Ottawa, Ontario Canada K2K 2M5

+1 613 599 8900 info@rbr-global.com rbr-global.com